




FGA 2 SI-55 N003

Технические данные

Attribute	Value
Материал присоски	Силикон SI
Твердость материала [Shore A]	55,0 Shore A
размер	2,00
Количество складок	1,5
Характеристики материала	Совместимый с FDA



Конструктивные данные FGA 2 SI-55 N003

Конструктивные данные

Attribute	Value
Высота H2	1,50 mm
Высота H	4,50 mm
Наружный диаметр D1	3,3 mm
Диаметр головки Dk	4,0 mm
Внутренний диаметр d1	3,0 mm
d2	1,3 mm
Внутренний диаметр d	2,00 mm
Ход пружины Z	1,0 mm
Диаметр Ds	1,9 mm
Высота H3	2,30 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Art.-Nr.: 10.01.06.04518



Технические данные

Attribute	Value
Материал присоски	Силикон SI
Радиус заготовки мин. (выпуклый)	1,0 mm
Всасывающая сила (-600 мбар)	0,08 N
Вес	0,0 g
размер	2,00
Количество складок	1,5
Семейство продуктов	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04518



WWW.SCHMALZ.COM/10.01.06.04518