

Сильфонная присоска (круглая)

FGB 12 SI-55 N016

Art.-Nr.: 10.01.06.04502



FGB 12 SI-55 N016

Технические данные

Attribute	Value
Материал присоски	Силикон SI
Твердость материала [Shore A]	55,0 Shore A
размер	12,00
Количество складок	3,5

Конструктивные данные

Attribute	Value
Высота H2	6,50 mm
Высота H	24,50 mm
Наружный диаметр D1	12,0 mm
Диаметр головки Dk	10,0 mm
d2	5,0 mm
Внутренний диаметр d	4,50 mm
Ход пружины Z	11,0 mm
Диаметр Ds	11,9 mm
Диаметр Dmax(S)	13,0 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные FGB 12 SI-55 N016



WWW.SCHMALZ.COM/10.01.06.04502

Art.-Nr.: 10.01.06.04502



Технические данные

Attribute	Value
Материал присоски	Силикон SI
Всасывающая сила (-600 мбар)	1,18 N
Вес	1,3 g
Объем	0,958 cm ³
размер	12,00
Количество складок	3,5
Семейство продуктов	FGB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04502

