



FGA 2 HT1-60 N003


Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	2.00
Körük Sayısı	1.5

Tasarım verileri

Attribute	Value
Yükseklik H2	1.50 mm
Yükseklik H	4.50 mm
Dış çap D1	3.3 mm
Kafa çapı Dk	4.0 mm
İç çap d1	3.0 mm
d2	1.3 mm
İç çap d	2.00 mm
Yay stroku Z	1.0 mm
Çap Ds	1.9 mm
Yükseklik H3	2.30 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 2 HT1-60 N003

Körüklü vantuz (yuvarlak)

FGA 2 HT1-60 N003



Art.-Nr.: 10.01.06.04519



Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
İş parçası yarıçapı dak (dışbükey)	1.0 mm
Emme kuvveti (-600mbar)	0.08 N
Ağırlık	0.0 g
Boyut	2.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04519



WWW.SCHMALZ.COM/10.01.06.04519