


Körüklü vantuz (yuvarlak)

FG 52 SI-MD-55 N018




Art.-Nr.: 10.01.06.04882



FG 52 SI-MD-55 N018

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	52.00
Körük Sayısı	2.5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FG 52 SI-MD-55 N018

Tasarım verileri

Attribute	Value
Yükseklik H2	13.00 mm
Yükseklik H	48.70 mm
Dış çap D1	52.0 mm
Kafa çapı Dk	18.0 mm
d2	24.6 mm
İç çap d	8.00 mm
Yay stroku Z	25.0 mm
Çap Ds	52.5 mm
Çap Dmax(S)	55.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.06.04882

Art.-Nr.: 10.01.06.04882

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 018
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
İş parçası yarıçapı dak (dışbükey)	75.0 mm
Çekme kuvveti	96.00 N
Emme kuvveti (-600mbar)	28.52 N
Ağırlık	22.9 g
Cilt	37.587 cm ³
Boyut	52.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04882

WWW.SCHMALZ.COM/10.01.06.04882