

Art.-Nr.: 10.01.06.04898



SAOB 60x30 NBR-60 G1/4-IG MOD

Suction cup SAOB, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.


### Technical data

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Number of folds	1.5
Connection	G1/4-IG

### Design data

Length L1	55.70 mm
Width B1	31.00 mm
Height H	33.30 mm
Nominal diameter dn	4.00 mm
Thread G1	G1/4"-F
Thread length LG1	11.0 mm
Key width SW1	22.0 mm
Spring stroke Z	7.0 mm
Suction cup width Bs	30.60 mm
Ls	60.60 mm
Lmax.(S)	63.00 mm
Bmax(S)	33.00 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



16.01.01.03426  
SAOB 110x55 NBR-60 G1/4-IG FO  
(10.01.06.04900)

Design data SAOB 60x30 NBR-60 G1/4-IG MOD



Art.-Nr.: 10.01.06.04898

**Technical data**

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	18.0 mm
Pull-off force	69.50 N
Suction force (-600mbar)	38.00 N
Weight	69.00 g
Lateral force	72.5 N
Lateral force oily surface	41.7 N
Volume	10.500 cm <sup>3</sup>
Number of folds	1.5
Product family	SAOB

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.06.04898**

Typ		Item number
Suction-cup connection (rigid)	SAUG-ANB G1/4-AG 200 MOD	10.01.03.00343
Universal holder	HTR-UNI 2N G19 140 MOD	10.01.03.00344
Suction-cup connection (rigid)	SAUG-ANB G1/4-AG 140 MOD	10.01.03.00345
Suction-cup connection (rigid)	SAUG-ANB G1/4-AG 80 MOD	10.01.03.00352
Universal holder	HTR-UNI 2N G19 80 MOD	10.01.03.00353

