

Art.-Nr.: 10.01.06.04900




Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Number of folds	1.5
Connection	G1/4-IG

SAOB 110x55 NBR-60 G1/4-IG MOD

Suction cup SAOB, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



16.01.01.03426
SAOB 110x55 NBR-60 G1/4-IG FO
(10.01.06.04900)

Design data

Attribute	Value
Length L1	98.80 mm
Width B1	53.00 mm
Height H	41.90 mm
Nominal diameter dn	4.00 mm
Thread G1	G1/4"-F
Thread length LG1	11.0 mm
Key width SW1	22.0 mm
Spring stroke Z	12.0 mm
Suction cup width Bs	55.10 mm
Ls	110.10 mm
Lmax.(S)	114.00 mm
Bmax(S)	59.00 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SAOB 110x55 NBR-60 G1/4-IG MOD



SAOB 110x55 NBR-60 G1/4-IG MOD

Art.-Nr.: 10.01.06.04900



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	50.0 mm
Pull-off force	233.50 N
Suction force (-600mbar)	110.00 N
Weight	138.00 g
Lateral force	299.2 N
Lateral force oily surface	123.6 N
Volume	53.100 cm ³
Number of folds	1.5
Product family	SAOB

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04900



Ordering Data Accessories 10.01.06.04900

Typ		Item number
Suction-cup connection (rigid)	SAUG-ANB G1/4-AG 200 MOD	10.01.03.00343
Universal holder	HTR-UNI 2N G19 140 MOD	10.01.03.00344
Suction-cup connection (rigid)	SAUG-ANB G1/4-AG 140 MOD	10.01.03.00345
Suction-cup connection (rigid)	SAUG-ANB G1/4-AG 80 MOD	10.01.03.00352
Universal holder	HTR-UNI 2N G19 80 MOD	10.01.03.00353

