

Сильфонная присоска (круглая)
FGC 50 NBR-55 SC080




Art.-Nr.: 10.01.06.04920



FGC 50 NBR-55 SC080

Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	55,0 Shore A
размер	50,00
Количество складок	4,5
Семейство ниппелей с интерфейсом	SC080



Конструктивные данные FGC 50 NBR-55 SC080

Конструктивные данные

Attribute	Value
Высота H2	13,00 mm
Высота H	55,00 mm
Наружный диаметр D1	49,5 mm
Диаметр головки Dk	26,5 mm
d2	34,5 mm
Внутренний диаметр d	16,00 mm
Ход пружины Z	31,0 mm
Диаметр Ds	47,0 mm
Диаметр Dmax(S)	51,0 mm



WWW.SCHMALZ.COM/10.01.06.04920

Сильфонная присоска (круглая)
FGC 50 NBR-55 SC080



Art.-Nr.: 10.01.06.04920



Технические данные

Attribute	Value
Семейство ниппелей	SC 080
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	55,0 Shore A
Всасывающая сила (-600 мбар)	55,00 N
размер	50,00
Количество складок	4,5
Семейство продуктов	FGC

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04920



WWW.SCHMALZ.COM/10.01.06.04920