


Art.-Nr.: 10.01.06.05502



PSPF 33 SI-30/55 SC080

Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	30.0 Shore A
Size	33.00
Number of folds	3.5
Material hardness	55.0 Shore A
Material characteristics	FDA-compatible



Design data PSPF 33 SI-30/55 SC080

Design data

Attribute	Value
Height H2	13.00 mm
Height H	40.00 mm
Head diameter Dk	21.0 mm
Internal diameter d1	19.6 mm
d2	14.0 mm
Internal diameter d	16.00 mm
Spring stroke Z	14.5 mm
Diameter Ds	33.0 mm
Height H3	14.40 mm
Diameter Dmax(S)	33.5 mm

Art.-Nr.: 10.01.06.05502

**Technical data**

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	30.0 Shore A
Suction force (-600mbar)	24.00 N
Volume	7.500 cm ³
Size	33.00
Number of folds	3.5
Material hardness	55.0 Shore A
Product family	PSPF
Material characteristics	FDA-compatible

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05502

