



FGA 8 SI-40 N063


Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	40.0 Shore A
Boyut	8.00
Körük Sayısı	1.5

Tasarım verileri

Attribute	Value
Yükseklik H2	3.40 mm
Yükseklik H	11.80 mm
Dış çap D1	9.4 mm
Kafa çapı Dk	5.5 mm
d2	3.5 mm
İç çap d	1.90 mm
Yay stroku Z	3.6 mm
Çap Ds	8.0 mm
Çap Dmax(S)	9.7 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 8 SI-40 N063

Körüklü vantuz (yuvarlak)

FGA 8 SI-40 N063



Art.-Nr.: 10.01.06.05688



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
İş parçası yarıçapı dak (dışbükey)	4.0 mm
Emme kuvveti (-600mbar)	0.58 N
Boyut	8.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05688



Veri aksesuarları sipariş edin 10.01.06.05688

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N063 M3-AG DN100
	10.01.06.05727



WWW.SCHMALZ.COM/10.01.06.05688