

Körüklü vantuz (yuvarlak)

## FG 18 SI-MD-55 N016

Art.-Nr.: 10.01.06.05700



FG 18 SI-MD-55 N016


### Teknik veriler

| Attribute                  | Value                          |
|----------------------------|--------------------------------|
| Vantuz malzemesi           | Silikon SI metal algılanabilir |
| Malzeme sertliği [Shore A] | 55,0 Shore A                   |
| Boyut                      | 18,00                          |
| Körük Sayısı               | 2,5                            |

### Tasarım verileri

| Attribute    | Value    |
|--------------|----------|
| Yükseklik H2 | 3,80 mm  |
| Yükseklik H  | 22,60 mm |
| Dış çap D1   | 17,8 mm  |
| Kafa çapı Dk | 10,0 mm  |
| d2           | 8,0 mm   |
| İç çap d     | 4,50 mm  |
| Yay stroku Z | 9,0 mm   |
| Çap Ds       | 17,2 mm  |
| Yükseklik H3 | 9,00 mm  |
| Çap Dmax(S)  | 19,0 mm  |

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FG 18 SI-MD-55 N016



[WWW.SCHMALZ.COM/10.01.06.05700](http://WWW.SCHMALZ.COM/10.01.06.05700)

Art.-Nr.: 10.01.06.05700

**Teknik veriler**

| Attribute                          | Value                          |
|------------------------------------|--------------------------------|
| Meme ucu ailesi                    | N 016                          |
| Vantuz malzemesi                   | Silikon SI metal algılanabilir |
| Malzeme sertliği [Shore A]         | 55,0 Shore A                   |
| İş parçası yarıçapı dak (dışbükey) | 9,0 mm                         |
| Çekme kuvveti                      | 8,50 N                         |
| Emme kuvveti (-600mbar)            | 3,02 N                         |
| Ağırlık                            | 1,90 g                         |
| Cilt                               | 1,648 cm <sup>3</sup>          |
| Boyut                              | 18,00                          |
| Körük Sayısı                       | 2,5                            |
| Ürün ailesi                        | FG                             |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.06.05700](http://www.schmalz.com/10.01.06.05700)

[WWW.SCHMALZ.COM/10.01.06.05700](http://WWW.SCHMALZ.COM/10.01.06.05700)