


Körüklü vantuz (yuvarlak)

FG 20 SI-MD-55 N016



Art.-Nr.: 10.01.06.05701



FG 20 SI-MD-55 N016


Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	20.00
Körük Sayısı	2.5

Tasarım verileri

Attribute	Value
Yükseklik H2	3.80 mm
Yükseklik H	22.10 mm
Dış çap D1	20.0 mm
Kafa çapı Dk	10.0 mm
d2	10.5 mm
İç çap d	4.50 mm
Yay stroku Z	9.0 mm
Çap Ds	20.0 mm
Yükseklik H3	9.00 mm
Çap Dmax(S)	21.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FG 20 SI-MD-55 N016



WWW.SCHMALZ.COM/10.01.06.05701

Art.-Nr.: 10.01.06.05701

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 016
Vantuz malzemesi	Silikon Si metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
İş parçası yarıçapı dak (dışbükey)	10.0 mm
Çekme kuvveti	12.10 N
Emme kuvveti (-600mbar)	5.20 N
Ağırlık	2.3 g
Cilt	2.298 cm ³
Boyut	20.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05701

WWW.SCHMALZ.COM/10.01.06.05701