

Art.-Nr.: 10.01.06.05531



SDC2 20 PU 30/60 G1/8-AG


The suction cup SDC2 , available in various diameters, is supplied with the connection nipple assembled.

Technical data

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	30.0 Shore A
Size	20.00
Number of folds	2.5
Material hardness	60.0 Shore A
Connection	G1/8-AG

Design data

Attribute	Value
Height H	14.50 mm
Outside diameter D1	20.0 mm
Head diameter Dk	12.0 mm
Nominal diameter dn	4.00 mm
d2	11.5 mm
Thread length LG1	7.5 mm
Key width SW1	13.0 mm
Spring stroke Z	7.5 mm
Diameter Ds	21.0 mm
Height H3	6.50 mm



Design data SDC2 20 PU 30/60 G1/8-AG

Art.-Nr.: 10.01.06.05531

**Technical data**

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	30.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	10.0 mm
Pull-off force	15.00 N
Suction force (-600mbar)	6.20 N
Volume	1.500 cm ³
Size	20.00
Temperature resistance	55.0 °C
Number of folds	2.5
Material hardness	60.0 Shore A
Connection	G1/8-AG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05531

**Ordering Data Spare Parts 10.01.06.05531**

Typ		Item number
Bellows suction cup 2C (round)	SDC2 20 PU 30/60 N042	10.01.06.03365
Suction cup connection nipple	SA-NIP N042 G1/8-AG DN400	10.01.06.03370

