

Bellows suction cups (round)

FSG 9 SI-MD-55 M5-AG




Art.-Nr.: 10.01.06.05705



FSG 9 SI-MD-55 M5-AG

Technical data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Size	9.00
Number of folds	2.5
Connection	M5-M
Nipple material	Aluminum
Material characteristics	FDA-compatible



Design data FSG 9 SI-MD-55 M5-AG

Design data

Attribute	Value
Height H	20.00 mm
Nominal diameter dn	2.50 mm
d2	4.1 mm
Thread G1	M5-M
Thread length LG1	5.0 mm
Key width SW1	7.0 mm
Spring stroke Z	3.0 mm
Diameter Ds	9.0 mm
Diameter Dmax(S)	9.5 mm



WWW.SCHMALZ.COM/10.01.06.05705

Bellows suction cups (round)

FSG 9 SI-MD-55 M5-AG



Art.-Nr.: 10.01.06.05705



Technical data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	10.0 mm
Pull-off force	2.30 N
Suction force (-600mbar)	0.79 N
Weight	1.8 g
Volume	0.150 cm ³
Size	9.00
Number of folds	2.5
Product family	FSG
Connection	M5-AG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05705



Ordering Data Spare Parts 10.01.06.05705

Typ		Item number
Bellows suction cup (round)	FG 9 SI-MD-55 N016	10.01.06.04244
Suction cup connection nipple	SA-NIP N016 M5-AG DN250	10.01.06.00123



WWW.SCHMALZ.COM/10.01.06.05705