





FSG 18 SI-MD-55 G1/8-IG

Technical data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Size	18.00
Number of folds	2.5
Connection	G1/8"-F
Nipple material	Aluminum
Material characteristics	FDA-compatible



Design data FSG 18 SI-MD-55 G1/8-IG

Design data

Attribute	Value
Height H	34.60 mm
Nominal diameter dn	3.50 mm
d2	8.0 mm
Thread G1	G1/8"-F
Thread length LG1	8.5 mm
Key width SW1	14.0 mm
Spring stroke Z	9.0 mm
Diameter Ds	17.2 mm
Diameter Dmax(S)	19.0 mm

Art.-Nr.: 10.01.06.05712

**Technical data**

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Pull-off force	8.50 N
Suction force (-600mbar)	3.02 N
Weight	6.0 g
Volume	1.350 cm ³
Size	18.00
Number of folds	2.5
Product family	FSG
Connection	G1/8-IG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05712

**Ordering Data Spare Parts 10.01.06.05712**

Typ		Item number
Bellows suction cup (round)	FG 18 SI-MD-55 N016	10.01.06.05700
Suction cup connection nipple	SA-NIP N016 G1/8-IG DN350	10.01.06.05731

