




FSG 9 SI-MD-55 G1/8-AG

Technical data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Size	9.00
Number of folds	2.5
Connection	G1/8"-M
Nipple material	Aluminum
Material characteristics	FDA-compatible



Design data FSG 9 SI-MD-55 G1/8-AG

Design data

Attribute	Value
Height H	21.00 mm
Nominal diameter dn	3.50 mm
d2	4.1 mm
Thread G1	G1/8"-M
Thread length LG1	7.5 mm
Key width SW1	14.0 mm
Spring stroke Z	3.0 mm
Diameter Ds	9.0 mm
Diameter Dmax(S)	9.5 mm

Art.-Nr.: 10.01.06.05704

**Technical data**

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	10.0 mm
Pull-off force	2.30 N
Suction force (-600mbar)	0.79 N
Weight	4.5 g
Volume	0.150 cm ³
Size	9.00
Number of folds	2.5
Product family	FSG
Connection	G1/8-AG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05704

**Ordering Data Spare Parts 10.01.06.05704**

Typ		Item number
Bellows suction cup (round)	FG 9 SI-MD-55 N016	10.01.06.04244
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN350	10.01.06.05735

