




FSG 12 SI-MD-55 G1/8-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	12.00
Körük Sayısı	2.5
Bağlantı	G1/8"-M
Meme ucu malzemesi	Alüminyum
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FSG 12 SI-MD-55 G1/8-AG

Tasarım verileri

Attribute	Value
Yükseklik H	27.00 mm
Nominal çap dn	3.50 mm
d2	5.0 mm
Diş G1	G1/8"-M
Diş uzunluğu LG1	7.5 mm
Anahtar boyutu SW1	14.0 mm
Yay stroku Z	7.0 mm
Çap Ds	12.0 mm
Çap Dmax(S)	13.0 mm

Art.-Nr.: 10.01.06.05707

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	4.0 mm
İş parçası yarıçapı dak (dışbükey)	12.5 mm
Çekme kuvveti	3.50 N
Emme kuvveti (-600mbar)	1.18 N
Ağırlık	4.9 g
Cilt	0.600 cm ³
Boyut	12.00
Körük Sayısı	2.5
Ürün ailesi	FSG
Bağlantı	G1/8-AG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05707

**Yedek parçalar için sipariş verileri 10.01.06.05707**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	FG 12 SI-MD-55 N016 10.01.06.04134
Vantuz bağlantı nipel	SA-NIP N016 G1/8-AG DN350 10.01.06.05735

