




FSG 14 SI-MD-55 G1/8-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	14.00
Körük Sayısı	2.5
Bağlantı	G1/8"-F
Meme ucu malzemesi	Alüminyum
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FSG 14 SI-MD-55 G1/8-IG

Tasarım verileri

Attribute	Value
Yükseklik H	34.80 mm
Nominal çap dn	3.50 mm
d2	5.4 mm
Diş G1	G1/8"-F
Diş uzunluğu LG1	8.5 mm
Anahtar boyutu SW1	14.0 mm
Yay stroku Z	9.0 mm
Çap Ds	14.5 mm
Çap Dmax(S)	15.5 mm

Art.-Nr.: 10.01.06.05709

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	4.0 mm
İş parçası yarıçapı dak (dışbükey)	15.0 mm
Çekme kuvveti	5.70 N
Emme kuvveti (-600mbar)	1.37 N
Ağırlık	5.7 g
Cilt	0.975 cm ³
Boyut	14.00
Körük Sayısı	2.5
Ürün ailesi	FSG
Bağlantı	G1/8-IG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05709

**Yedek parçalar için sipariş verileri 10.01.06.05709**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	FG 14 SI-MD-55 N016 10.01.06.03982
Vantuz bağlantı nipel	SA-NIP N016 G1/8-IG DN350 10.01.06.05731

