

Bellows suction cups (round)

FSG 32 SI-MD-55 G1/4-IG




Art.-Nr.: 10.01.06.05720



FSG 32 SI-MD-55 G1/4-IG

Technical data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Size	32.00
Number of folds	2.5
Connection	G1/4"-F
Nipple material	Aluminum
Material characteristics	FDA-compatible



Design data FSG 32 SI-MD-55 G1/4-IG

Design data

Attribute	Value
Height H	52.50 mm
Nominal diameter dn	4.40 mm
d2	16.0 mm
Thread G1	G1/4"-F
Thread length LG1	12.0 mm
Key width SW1	17.0 mm
Spring stroke Z	15.0 mm
Diameter Ds	32.0 mm
Diameter Dmax(S)	33.5 mm



WWW.SCHMALZ.COM/10.01.06.05720

Art.-Nr.: 10.01.06.05720

**Technical data**

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	35.0 mm
Pull-off force	36.90 N
Suction force (-600mbar)	12.06 N
Weight	18.0 g
Volume	10.000 cm ³
Size	32.00
Number of folds	2.5
Product family	FSG
Connection	G1/4-IG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05720

**Ordering Data Spare Parts 10.01.06.05720**

Typ		Item number
Bellows suction cup (round)	FG 32 SI-MD-55 N018	10.01.06.04526
Suction cup connection nipple	SA-NIP N018 G1/4-IG DN440	10.01.06.01066

