



Art.-Nr.: 10.01.06.05711



FSG 14 SI-MD-55 M5-AG

Technical data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Size	14.00
Number of folds	2.5
Connection	M5-M
Nipple material	Aluminum
Material characteristics	FDA-compatible



Design data FSG 14 SI-MD-55 M5-AG

Design data

Attribute	Value
Height H	27.80 mm
Nominal diameter dn	2.50 mm
d2	5.4 mm
Thread G1	M5-M
Thread length LG1	5.0 mm
Key width SW1	7.0 mm
Spring stroke Z	9.0 mm
Diameter Ds	14.5 mm
Diameter Dmax(S)	15.5 mm

Art.-Nr.: 10.01.06.05711

**Technical data**

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	15.0 mm
Pull-off force	5.70 N
Suction force (-600mbar)	1.37 N
Weight	2.6 g
Volume	0.975 cm ³
Size	14.00
Number of folds	2.5
Product family	FSG
Connection	M5-AG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05711

**Ordering Data Spare Parts 10.01.06.05711**

Typ		Item number
Bellows suction cup (round)	FG 14 SI-MD-55 N016	10.01.06.03982
Suction cup connection nipple	SA-NIP N016 M5-AG DN250	10.01.06.00123

