


Art.-Nr.: 10.01.06.05751



SDC2 50 PU 30/60 G1/4-AG

The suction cup SDC2 , available in various diameters, is supplied with the connection nipple assembled.



Design data SDC2 50 PU 30/60 G1/4-AG

Technical data

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	30.0 Shore A
Size	50.00
Number of folds	2.5
Material hardness	60.0 Shore A
Connection	G1/4-AG

Design data

Attribute	Value
Height H	41.50 mm
Outside diameter D1	42.5 mm
Head diameter Dk	27.5 mm
Nominal diameter dn	8.00 mm
d2	21.9 mm
Thread length LG1	10.0 mm
Key width SW1	24.0 mm
Spring stroke Z	16.0 mm
Diameter Ds	50.0 mm
Height H3	14.40 mm

Art.-Nr.: 10.01.06.05751

**Technical data**

Attribute	Value
Suction cup material	Polyurethane PU
Material hardness [Shore A]	30.0 Shore A
Hose inner diameter (recom.) d	9.0 mm
Workpiece radius min. (convex)	20.0 mm
Pull-off force	72.00 N
Suction force (-600mbar)	22.60 N
Volume	19.500 cm ³
Size	50.00
Temperature resistance	55.0 °C
Number of folds	2.5
Material hardness	60.0 Shore A
Connection	G1/4-AG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05751

**Ordering Data Spare Parts 10.01.06.05751**

Typ		Item number
Bellows suction cup 2C (round)	SDC2 50 PU 30/60 N044	10.01.06.03368
Suction cup connection nipple	SA-NIP N044 G1/4-AG DN800	10.01.06.05750

