

Bellows suction cups (round)

FSG 20 SI-MD-55 G1/8-AG




Art.-Nr.: 10.01.06.05716



Technical data

Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Size	20.00
Number of folds	2.5
Connection	G1/8"-M
Nipple material	Aluminum
Material characteristics	FDA-compatible

FSG 20 SI-MD-55 G1/8-AG



Design data

Height H	28.10 mm
Nominal diameter dn	3.50 mm
d2	10.5 mm
Thread G1	G1/8"-M
Thread length LG1	7.5 mm
Key width SW1	14.0 mm
Spring stroke Z	9.0 mm
Diameter Ds	20.0 mm
Diameter Dmax(S)	21.0 mm

Design data FSG 20 SI-MD-55 G1/8-AG



WWW.SCHMALZ.COM/10.01.06.05716

Art.-Nr.: 10.01.06.05716

**Technical data**

Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	30.0 mm
Pull-off force	12.10 N
Suction force (-600mbar)	5.20 N
Weight	6.00 g
Volume	2.298 cm ³
Size	20.00
Number of folds	2.5
Product family	FSG
Connection	G1/8-AG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Spare Parts 10.01.06.05716**

Typ		Item number
Bellows suction cup (round)	FG 20 SI-MD-55 N016	10.01.06.05701
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN350	10.01.06.05735

