


Art.-Nr.: 10.01.06.06033



SAOXB 110x55 ED-85 RA MOD



Design data SAOXB 110x55 ED-85 RA MOD

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Number of folds	1.5
Dimension (LxW)	110x55
Nipple material	Aluminum

Design data

Attribute	Value
Length L1	108.50 mm
Width B1	53.30 mm
Height H	42.00 mm
Nominal diameter dn	4.50 mm
Spring stroke Z	17.0 mm
Length L4	31.80 mm
Suction cup width Bs	54.00 mm
Ls	110.00 mm
Key width SW3	5.0 mm
Lmax.(S)	114.00 mm
Bmax(S)	60.00 mm
Length L2	89.00 mm
Width B2	33.50 mm

SAOXB 110x55 ED-85 RA MOD

Art.-Nr.: 10.01.06.06033



Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Workpiece radius min. (convex)	25.0 mm
Pull-off force	190.10 N
Suction force (-600mbar)	155.00 N
Lateral force	91.7 N
Lateral force oily surface	97.6 N
Volume	72.300 cm ³
Number of folds	1.5
Effective suction area	49.73 mm ²
Product family	SAOXB
Dimension (LxW)	110x55
Nipple material	Aluminum

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.06033



Ordering Data Spare Parts 10.01.06.06033

Typ	Item number
Bellows suction cup (oval)	SAOXB 110x55 ED-85 SC043 10.01.06.05783

