




SAOXB 60x30 ED-85 SC043

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Körük Sayısı	1,5
Boyutlar (LxW)	60x30

Tasarım verileri

Attribute	Value
Uzunluk L1	59,20 mm
Genişlik B1	29,50 mm
Yükseklik H2	1,50 mm
Yükseklik H	25,00 mm
Kafa uzunluğu Lk	41,00 mm
Yay stroku Z	10,5 mm
Vantuz genişliği Bs	30,00 mm
Ls	60,00 mm
Lmaks.(S)	63,00 mm
Bmaks(S)	34,00 mm
Bk	23,00 mm
Uzunluk L2	45,60 mm
Genişlik B2	15,60 mm



Tasarım verileri SAOXB 60x30 ED-85 SC043

Körüklü vantuz (oval)

SAOXB 60x30 ED-85 SC043



Art.-Nr.: 10.01.06.05781



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Ürün ailesi	SAOXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05781



WWW.SCHMALZ.COM/10.01.06.05781