

Art.-Nr.: 10.01.06.05783




SAOXB 110x55 ED-85 SC043

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Number of folds	1.5
Dimension (LxW)	110x55

Design data

Attribute	Value
Length L1	108.50 mm
Width B1	53.30 mm
Height H2	1.50 mm
Height H	34.40 mm
Head length Lk	79.30 mm
Spring stroke Z	17.0 mm
Suction cup width Bs	54.00 mm
Ls	110.00 mm
Lmax.(S)	114.00 mm
Bmax(S)	60.00 mm
Bk	34.00 mm
Length L2	89.00 mm
Width B2	33.50 mm



Design data SAOXB 110x55 ED-85 SC043

Bellows suction cup (oval)

SAOXB 110x55 ED-85 SC043



Art.-Nr.: 10.01.06.05783



Technical data

Attribute	Value
Suction cup material	Elastodur ED
Product family	SAOXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05783



WWW.SCHMALZ.COM/10.01.06.05783