

Vacuum lifting cylinder

HS 14-22 M5-IG



Art.-Nr.: 10.01.07.00014




Technical data

Attribute	Value
Suction cup connection	M5-F
Vacuum connection	G1/8"-F
Stroke Z	14.00 mm

HS 14-22 M5-IG

Vacuum lifting cylinder HS is delivered as a ready to connect product with the desired properties. The delivery does not include a suction cup.



Design data

Attribute	Value
Length L	30.00 mm
Height H1	43.50 mm
Height H2	5.50 mm
Height H	65.50 mm
Outside diameter D1	9.0 mm
Outside diameter D	31.00 mm
Thread G1	G1/8"-F
Thread length LG1	5.0 mm
Thread G2	M5-F
Thread length LG2	10.0 mm

Design data HS 14-22 M5-IG



WWW.SCHMALZ.COM/10.01.07.00014

Vacuum lifting cylinder
HS 14-22 M5-IG



Art.-Nr.: 10.01.07.00014



Technical data

Attribute	Value
Weight	0.130 kg
Air consumption [l/min]	33.3 l/min
Air consumption	1.998 m ³ /h
Holding force	3.5 N
Cycle time	0.8 s
Product family	HS



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.07.00014



WWW.SCHMALZ.COM/10.01.07.00014