

**Technical data**

Attribute	Value
Air consumption [l/min]	48.0 l/min
Air consumption	2.880 m ³ /h
Suction rate	2.300 m ³ /h
Outside diameter D	210.00 mm

VC-M-SP 210

The Multi-Clamp system is delivered assembled. The product consists of:

- Suction plate with sealing
- Multi-Base with turning and swivelling unit
- Vacuum hose

Available spare parts: friction insert, sealing profile

Available accessories: Multi-Base VC-M-B, Multi-Clamp suction plate VC-M-SP, Multi-Base VC-M-BV, Multi-Clamp suction plate VC-M-SPV, Multi-Clamp vacuum pump VC-M-PU, foot-operated interrupter FU, accessories

Design data

Attribute	Value
-----------	-------

Design data VC-M-SP 210

**Technical data**

Attribute	Value
Weight	1.647 kg



Multi-Clamp - Suction plate

VC-M-SP 210



Art.-Nr.: 10.01.12.02002



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.02002



WWW.SCHMALZ.COM/10.01.12.02002