



Art.-Nr.: 10.01.06.06017



SAOXB 80x40 ED-85 NPT3/8-IG



Design data SAOXB 80x40 ED-85 NPT3/8-IG

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Number of folds	1.5
Dimension (LxW)	80x40
Nipple material	Brass

Design data

Attribute	Value
Length L1	78.80 mm
Width B1	39.00 mm
Height H	42.70 mm
Nominal diameter dn	4.50 mm
Thread G1	NPT3/8"-F
Thread length LG1	12.0 mm
Key width SW1	22.0 mm
Spring stroke Z	14.0 mm
Suction cup width Bs	39.00 mm
Ls	80.00 mm
Key width SW3	5.0 mm
Lmax.(S)	84.00 mm
Bmax(S)	46.00 mm
Length L2	63.00 mm
Width B2	23.00 mm

Art.-Nr.: 10.01.06.06017

**Technical data**

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Workpiece radius min. (convex)	17.5 mm
Pull-off force	96.60 N
Suction force (-600mbar)	76.10 N
Lateral force	42.8 N
Lateral force oily surface	50.4 N
Volume	30.900 cm ³
Number of folds	1.5
Effective suction area	26.52 mm ²
Product family	SAOXB
Dimension (LxW)	80x40
Nipple material	Brass

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.06017

**Ordering Data Spare Parts 10.01.06.06017**

Typ	Item number
Bellows suction cup (oval)	SAOXB 80x40 ED-85 SC043 10.01.06.05782