

Art.-Nr.: 10.01.12.04752

**Technical data**

Attribute	Value
Height H	74.00 mm
Stroke Z	9.00 mm
Dimension (LxW)	150x135
Clamping range [mm]	15.0 ... 85.0 mm
Shape	QUICK


VCMC-B-QUICK 150x135x74 15-85

The mechanical clamp VCMC-B-QUICK is delivered assembled. The product consists of:

- Clamping disc with quick adjustment
- Main body made of aluminum
- Hexagonal bolts

Available spare parts: clamping disc

Available accessories: clamping range extension

**Design data**

Attribute	Value
Length L	146.40 mm
Width B	133.00 mm
Height H2	30.00 mm
Height H	74.00 mm
Hole spacing X1	66.5 mm
Hole spacing X2	44.0 mm
Stroke Z	9.00 mm

Design data VCMC-B-QUICK 150x135x74 15-85



Art.-Nr.: 10.01.12.04752



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.04752



Ordering Data Accessories 10.01.12.04752

Typ		Artikelnummer
Extension with hexagon	VRL-S M20x1x35	10.01.12.04374



Ordering Data Spare Parts 10.01.12.04752

Typ		Artikelnummer
Clamping disc	SPAN-TELL 110x30 EXZ VCMC	10.01.12.04688

