


Art.-Nr.: 10.01.12.04759

**Technical data**


Attribute	Value
Height H	100.00 mm
Stroke Z	10.00 mm
Dimension (LxW)	170x135
Clamping range [mm]	10.0 ... 100.0 mm
Shape	QUICK

VCMC-G-QUICK 170x135x100 10-100

The mechanical clamp VCMC-G-QUICK is delivered completely assembled. The product consists of:

- Clamping disc with quick adjustment
- Main body made of aluminum
- Sealing frame

Available spare parts: clamping disc, sealing frame

**Design data**

Attribute	Value
Length L	171.00 mm
Width B1	162.50 mm
Width B	133.00 mm
Height H1	233.50 mm
Height H	100.00 mm

Design data VCMC-G-QUICK 170x135x100 10-100



Mechanical clamp

VCMC-G-QUICK 170x135x100 10-100



Art.-Nr.: 10.01.12.04759



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.04759



Ordering Data Spare Parts 10.01.12.04759

Typ		Artikelnummer
Sealing frame (bottom)	VCDR 166x113x6.6 VCMC-G	10.01.12.04758
Clamping disc	SPAN-TELL 110 EXZ VCMC	10.01.12.04239



WWW.SCHMALZ.COM/10.01.12.04759