

Art.-Nr.: 10.01.12.04777

**Technical data**

Attribute	Value
Height H	110.00 mm
Stroke Z	10.00 mm
Dimension (LxW)	150x135
Clamping range [mm]	10.0 ... 100.0 mm
Shape	QUICK


VCMC-S6-QUICK 150x135x110 10-100

The mechanical clamp VCMC-S6-QUICK is delivered assembled. The product consists of:

- Clamping disc with quick adjustment
- Main body made of aluminum
- Dovetail mount

Available spare parts: clamping disc, sealing frame

Available accessories: clamping range extension

**Design data**

Attribute	Value
Length L	146.50 mm
Width B	133.00 mm
Height H1	248.40 mm
Height H2	30.00 mm
Height H	110.00 mm
Hole spacing X1	66.5 mm
Hole spacing X2	44.0 mm
Stroke Z	10.00 mm

Design data VCMC-S6-QUICK 150x135x110 10-100



Mechanical tensioner

VCMC-S6-QUICK 150x135x110 10-100



Art.-Nr.: 10.01.12.04777



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.04777



Ordering Data Spare Parts 10.01.12.04777

Typ		Artikelnummer
Sealing frame (bottom)	VCDR 135x25.5x6 VCBL	10.01.12.04560
Clamping disc	SPAN-TELL 110 EXZ VCMC	10.01.12.04239



WWW.SCHMALZ.COM/10.01.12.04777