


Art.-Nr.: 10.01.12.05284

**Technical data**

| Attribute                        | Value               |
|----------------------------------|---------------------|
| Height H                         | 100.00 mm           |
| Arrangement                      | insertable 360°/15° |
| Additional function vacuum block | Touch valve         |
| Dimension (LxW)                  | 170x128             |
| Shape                            | Heavy duty          |


VCBL-K1-HD 170x128x100 S-360-15 TV

The vacuum block VCBL-K1-HD is delivered assembled. The product consists of:

- Replaceable suction plate with sealing gasket, available in various dimensions
- Main body made of aluminum with mechanical clamping

Available spare parts: sealing gasket, suction plate

Available accessories: clamping

**Design data**

| Attribute | Value     |
|-----------|-----------|
| Length L1 | 170.00 mm |
| Length L  | 170.00 mm |
| Width B1  | 128.00 mm |
| Width B   | 128.00 mm |
| Height H1 | 107.00 mm |
| Height H  | 100.00 mm |

Design data VCBL-K1-HD 170x128x100 S-360-15 TV

Art.-Nr.: 10.01.12.05284

**Further documentation**CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.12.05284](http://www.schmalz.com/10.01.12.05284)**Ordering Data Spare Parts 10.01.12.05284**

| Typ                     |                                  | Artikelnummer  |
|-------------------------|----------------------------------|----------------|
| Suction plate (top)     | VCSP-O 170x128x19.5 RB AL        | 10.01.12.05226 |
| Sealing frame (bottom)  | VCDR 166x113x6.6 VCBL-K1         | 10.01.12.03629 |
| O-ring                  | O-RING 50x2.5 NBR-70             | 10.07.08.00073 |
| Touch Valve             | TV D9 4.3                        | 10.01.12.02514 |
| Machine screw           | SCHR 4762 M10x30 ST-8.8 VZ       | 20.01.02.02003 |
| Clamping unit           | KLEM-EINH 69.5x28.5x12.5 VCMC-K1 | 10.01.12.04835 |
| Sealing profile (meter) | DI-PROF 4x6 MOS NK-20 HR         | 10.07.04.00054 |

