

Art.-Nr.: 10.01.12.04612

**Technical data**

Attribute	Value
Height H	100.00 mm
Additional function vacuum block	Toolless height adjustment
Stroke Z	10.00 mm
Clamping range [mm]	10.0 ... 100.0 mm
Grid	30/40
Base area	150 x 130 mm
Shape	QUICK


VCMC-R-QUICK 150x130x100 30/40

The mechanical clamp VCMC-R-QUICK is delivered assembled. The product consists of:

- Clamping disc with quick adjustment
- Main body made of aluminum
- Sealing frame and mounting bracket

Available spare parts: clamping disc, sealing frame, mounting bracket

Available accessories: clamping range extension

**Design data**

Attribute	Value
Length L	148.50 mm
Width B	133.50 mm
Height H1	232.70 mm
Height H2	30.00 mm
Height H	100.00 mm
Outside diameter D1	56.0 mm
Hole spacing X1	66.5 mm
Hole spacing X2	44.0 mm

Design data VCMC-R-QUICK 150x130x100 30/40



Art.-Nr.: 10.01.12.04612

**Technical data**

Attribute	Value
Clamping range [mm]	10.0 ... 100.0 mm

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.04612

**Ordering Data Spare Parts 10.01.12.04612**

Typ		Artikelnummer
Clamping disc	SPAN-TELL 110 EXZ VCMC	10.01.12.04239
Set of spare parts	ERS VCBL-R Winkel	10.01.12.02691

