

Art.-Nr.: 10.01.12.04743

**Technical data**

Attribute	Value
Height H	125.00 mm
Additional function vacuum block	Toolless height adjustment
Stroke Z	10.00 mm
Dimension (LxW)	170x135
Clamping range [mm]	10.0 ... 100.0 mm
Shape	QUICK


VCMC-K2-QUICK 170x135x125 10-100

The mechanical clamp VCMC-K2-QUICK is delivered assembled. The product consists of:

- Clamping disc with quick adjustment
- Main body made of aluminum
- Mounting on the console

Available spare parts: clamping disc

Available accessories: mechanical clamping, conversion kit for automatic machine table, clamping range extension

**Design data**

Attribute	Value
Length L	170.00 mm
Width B	133.30 mm
Height H1	258.50 mm
Height H2	30.00 mm
Height H	125.00 mm
Outside diameter D1	56.0 mm
Hole spacing X1	66.5 mm
Hole spacing X2	44.0 mm

Design data VCMC-K2-QUICK 170x135x125 10-100



Art.-Nr.: 10.01.12.04743

**Technical data**

Attribute	Value
Clamping range [mm]	10.0 ... 100.0 mm

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.04743**Ordering Data Accessories 10.01.12.04743**

Typ	Artikelnummer
Clamping unit	KLEM-EINH 69.5x35x12.5 10.01.12.04990

**Ordering Data Spare Parts 10.01.12.04743**

Typ	Artikelnummer
Sealing frame (bottom)	VCDR 166x113x6.6 VCSP 10.01.12.02191
Clamping disc	SPAN-TELL 110 EXZ VCMC 10.01.12.04239

