

Art.-Nr.: 10.01.12.04760

**Technical data**

Attribute	Value
Height H	50.00 mm
Stroke Z	9.00 mm
Dimension (LxW)	145x145
Clamping range [mm]	15.0 ... 85.0 mm
Shape	QUICK

VCMC-S4-QUICK 145x145x50 15-85

The mechanical clamp VCMC-S4-QUICK is delivered completely assembled. The product consists of:


- Clamping disc with quick adjustment
- Main body made of aluminum
- Mounting for TVN console

Available spare parts: clamping disc, sealing frame

Available accessories: clamping range extension

Design data

Attribute	Value
Length L	145.00 mm
Width B	145.00 mm
Height H	50.00 mm
Hole spacing X1	66.5 mm
Hole spacing X2	44.0 mm
Stroke Z	9.00 mm



Design data VCMC-S4-QUICK 145x145x50 15-85



Art.-Nr.: 10.01.12.04760

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.04760**Ordering Data Accessories 10.01.12.04760**

Typ		Artikelnummer
Extension with hexagon	VRL-S M20x1x35	10.01.12.04374

**Ordering Data Spare Parts 10.01.12.04760**

Typ		Artikelnummer
Sealing frame (bottom)	VCDR 141x77.2x5.1 VCBL-S	10.01.12.03138
Clamping disc	SPAN-TELL 110x30 EXZ VCMC	10.01.12.04688