

Art.-Nr.: 10.01.12.04763

**Technical data**

Attribute	Value
Height H	45.00 mm
Additional function vacuum block	Toolless height adjustment
Stroke Z	9.00 mm
Clamping range [mm]	15.0 ... 85.0 mm
Grid	30/40/50
Base area	160 x 160 mm
Shape	QUICK


VCMC-R-QUICK 160x160x45 30/40/50

The mechanical clamp VCMC-R-QUICK is delivered assembled. The product consists of:

- Clamping disc with quick adjustment
- Main body made of aluminum
- Sealing frame and mounting bracket

Available spare parts: clamping disc, sealing frame, mounting bracket

Available accessories: clamping range extension

**Design data**

Attribute	Value
Length L	160.00 mm
Width B	160.00 mm
Height H1	162.50 mm
Height H2	30.00 mm
Height H	45.00 mm
Outside diameter D1	56.0 mm
Hole spacing X1	66.5 mm
Hole spacing X2	44.0 mm

Design data VCMC-R-QUICK 160x160x45 30/40/50



Art.-Nr.: 10.01.12.04763

**Technical data**

Attribute	Value
Clamping range [mm]	15.0 ... 85.0 mm

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.04763**Ordering Data Accessories 10.01.12.04763**

Typ	Artikelnummer
Extension with hexagon	VRL-S M20x1x35 10.01.12.04374

**Ordering Data Spare Parts 10.01.12.04763**

Typ	Artikelnummer
Sealing frame	ISDR 150x150x13.5 R 30/50 10.01.15.00352
Sealing frame	ISDR 120x120x13.5 R 30/40 10.01.15.00353
Clamping disc	SPAN-TELL 110x30 EXZ VCMC 10.01.12.04688
Set of spare parts	ERS VCBL-R Winkel 10.01.12.02691

