

Art.-Nr.: 10.01.15.00719



SSPB-117 117-125 NBR


Technical data

Attribute	Value
Sealing material	Perbunan
Height H1	137.00 mm
Diameter Ds	117.0 mm
Stroke Z	8.00 mm
Material workpiece support	ED
Working area [mm]	117.0 ... 125.0

The Basic Holding Fixture BHF clamping system from Schmalz is not supplied assembled. The system consists of several components which are ordered independently of each other:

- Uni-Base UB suitable for Schmalz Steel-Plate ISST-MPL or for a flat table
- Innospann Vacuum Cups ISCU^P
- Schmalz Balance SSPB suction plate with matching Innospann mounting

Available accessories: Reference suction cup



Design data SSPB-117 117-125 NBR

Design data

Attribute	Value
Height H1	137.00 mm
Outside diameter D	60.00 mm
Diameter Ds	117.0 mm
Stroke Z	8.00 mm
Operating height EH (min.)	117.00 mm
Operating height EH (max.)	125.00 mm



Schmalz Suction Plate Balance

SSPB-117 117-125 NBR



Art.-Nr.: 10.01.15.00719



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.15.00719



WWW.SCHMALZ.COM/10.01.15.00719