

Magnetic gripper (prepared f sensor)

SGM-SV 40 G1/4-IG




Art.-Nr.: 10.01.17.00229



Technical data

Attribute	Value
Size	40.00
Pressure range (operating pressure) [bar]	3.5 ... 6.0 bar
Holding force max. with friction ring	100.0 N
Socket	G1/4"-F

SGM-SV 40 G1/4-IG



Design data

Attribute	Value
Width B	40.65 mm
Height H	70.20 mm
Outside diameter D	40.00 mm
Internal diameter d	26.00 mm
Thread G1	G1/4"-F
Thread length LG1	11.0 mm
Thread G2	G1/8"-F
Thread length LG2	6.0 mm
Thread length LG4	7.0 mm
Hole spacing X1	46.0 mm

Design data SGM-SV 40 G1/4-IG



WWW.SCHMALZ.COM/10.01.17.00229

Art.-Nr.: 10.01.17.00229



Technical data

Attribute	Value
Weight	255.0 g
Installation position	BEL
Remaining holding force	0.3 N
Pressure range (operating pressure) [bar]	3.5 ... 6.0 bar
Operating temperature	5 ... 70 °C
Holding force max. with friction ring	100.0 N
Control valve	Bistable



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.17.00229



Ordering Data Accessories 10.01.17.00229

Typ	Item number
Sieve with male thread	SIEB G1/8x3.5 MS 0.27/0.15 ISKT 10.05.03.00008

