


Art.-Nr.: 10.01.17.00410



REIB-RING SGM-HT-HP 30 HT2-65

Technical data

Attribute	Value
Size	30
Utilization design	Magnetic gripper SGM-HT-HP
Outside diameter D	29.50 mm
Internal diameter d	20.50 mm

**Design data**

Attribute	Value
Length L	10.70 mm
Outside diameter D	29.50 mm

Design data REIB-RING SGM-HT-HP 30 HT2-65



Art.-Nr.: 10.01.17.00410



Technical data

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Weight	3.0 g
Size	30
Operating temperature max.	200.0 °C
Operating temperature max. short-term up to +250 °C	



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.17.00410

