


Art.-Nr.: 10.01.17.00412



REIB-RING SGM-HT-HP 50 HT2-65

Technical data

Attribute	Value
Size	50
Utilization design	Magnetic gripper SGM-HT-HP
Outside diameter D	50.00 mm
Internal diameter d	41.50 mm

**Design data**

Attribute	Value
Length L	10.70 mm
Outside diameter D	50.00 mm

Design data REIB-RING SGM-HT-HP 50 HT2-65



Art.-Nr.: 10.01.17.00412



Technical data

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Weight	4.7 g
Size	50
Operating temperature max.	200.0 °C
Operating temperature max. short-term up to +250 °C	



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.17.00412

