



Art.-Nr.: 10.01.17.00579



HTS-A5 SGM-HP 20 OP

**Technical data**

| Attribute          | Value                   |
|--------------------|-------------------------|
| Size               | 20                      |
| Utilization design | Magnetic gripper SGM-HP |
| Connection 1       | Ball head 32 mm         |



Design data HTS-A5 SGM-HP 20 OP

**Design data**

| Attribute           | Value    |
|---------------------|----------|
| Length L            | 63.00 mm |
| Width B             | 15.00 mm |
| Height H1           | 50.00 mm |
| Height H            | 9.40 mm  |
| Outside diameter D  | 32.00 mm |
| Internal diameter d | 3.40 mm  |
| Height H3           | 30.90 mm |
| Height H4           | 35.00 mm |
| Hole spacing Y1     | 6.5 mm   |
| Hole spacing X1     | 55.0 mm  |

**Technical data**

| Attribute | Value    |
|-----------|----------|
| Weight    | 68.3 g   |
| Material  | Aluminum |
| Size      | 20       |



Holder system

## HTS-A5 SGM-HP 20 OP



Art.-Nr.: 10.01.17.00579



**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.17.00579](http://www.schmalz.com/10.01.17.00579)



[WWW.SCHMALZ.COM/10.01.17.00579](http://WWW.SCHMALZ.COM/10.01.17.00579)