


Art.-Nr.: 10.01.17.00564



## Technical data

| Attribute          | Value                   |
|--------------------|-------------------------|
| Size               | 50                      |
| Utilization design | Magnetic gripper SGM-HP |
| Connection 1       | Ball head 32 mm         |

HTS-A5 SGM-HP 50 OP



## Design data

| Attribute           | Value     |
|---------------------|-----------|
| Length L            | 110.00 mm |
| Width B             | 29.00 mm  |
| Height H1           | 50.00 mm  |
| Height H2           | 6.00 mm   |
| Height H            | 9.40 mm   |
| Outside diameter D  | 32.00 mm  |
| Internal diameter d | 5.50 mm   |
| Height H3           | 30.90 mm  |
| Height H4           | 35.00 mm  |
| Hole spacing Y1     | 15.0 mm   |

Design data HTS-A5 SGM-HP 50 OP



## Technical data

| Attribute | Value    |
|-----------|----------|
| Weight    | 112.0 g  |
| Material  | Aluminum |
| Size      | 50       |

Holder system

## HTS-A5 SGM-HP 50 OP



Art.-Nr.: 10.01.17.00564



**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.17.00564](http://www.schmalz.com/10.01.17.00564)



[WWW.SCHMALZ.COM/10.01.17.00564](http://WWW.SCHMALZ.COM/10.01.17.00564)