




SAX 80 ED-85 G3/8-IG

Çeşitli çaplarda mevcut olan SAX vantuz, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.

## Teknik veriler

| Attribute                  | Value        |
|----------------------------|--------------|
| Vantuz malzemesi           | Elastodur ED |
| Malzeme sertliği [Shore A] | 85.0 Shore A |
| Boyut                      | 80.00        |
| Körük Sayısı               | 0.0          |
| Bağlantı                   | G3/8"-F      |



Tasarım verileri SAX 80 ED-85 G3/8-IG

## Tasarım verileri

| Attribute          | Value    |
|--------------------|----------|
| Yükseklik H        | 34.50 mm |
| Nominal çap dn     | 6.75 mm  |
| Diş G1             | G3/8"-F  |
| Diş uzunluğu LG1   | 12.0 mm  |
| Anahtar boyutu SW1 | 22.0 mm  |
| Yay stroku Z       | 13.9 mm  |
| Çap Ds             | 81.0 mm  |
| Çap Dmax(S)        | 92.2 mm  |

Art.-Nr.: 10.01.19.00141



## Teknik veriler

| Attribute                          | Value                  |
|------------------------------------|------------------------|
| Vantuz malzemesi                   | Elastodur ED           |
| Malzeme sertliği [Shore A]         | 85.0 Shore A           |
| İş parçası yarıçapı dak (dışbükey) | 32.5 mm                |
| Emme kuvveti (-600mbar)            | 270.00 N               |
| Ağırlık                            | 35.0 g                 |
| Yanal kuvvet                       | 192.0 N                |
| Yanal kuvvet yağlı yüzey           | 269.0 N                |
| Cilt                               | 51.000 cm <sup>3</sup> |
| Boyut                              | 80.00                  |
| Körük Sayısı                       | 0.0                    |
| Bağlantı                           | G3/8"-F                |
| Ürün ailesi                        | SAX                    |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



## Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.19.00141](http://www.schmalz.com/10.01.19.00141)

