




SAX 30 ED-85 G3/8-IG

Suction cup SAX, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Size	30.00
Number of folds	0.0
Connection	G3/8"-F

Design data



Attribute	Value
Height H	26.00 mm
Nominal diameter dn	6.75 mm
Thread G1	G3/8"-F
Thread length LG1	12.0 mm
Key width SW1	22.0 mm
Spring stroke Z	4.5 mm
Diameter Ds	31.7 mm
Diameter Dmax(S)	35.2 mm

Design data SAX 30 ED-85 G3/8-IG

Art.-Nr.: 10.01.19.00146

**Technical data**

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Workpiece radius min. (convex)	18.0 mm
Suction force (-600mbar)	39.00 N
Weight	24.0 g
Lateral force	38.0 N
Lateral force oily surface	41.0 N
Volume	3.200 cm ³
Size	30.00
Number of folds	0.0
Connection	G3/8"-F
Product family	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00146

