

Çan vantuz (yuvarlak)

## SAX 40 ED-85 G1/4-IG RP



Art.-Nr.: 10.01.19.00180




SAX 40 ED-85 G1/4-IG RP

Çeşitli çaplarda mevcut olan SAX vantuz, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.

### Teknik veriler

|                            |              |
|----------------------------|--------------|
| Vantuz malzemesi           | Elastodur ED |
| Malzeme sertliği [Shore A] | 85,0 Shore A |
| Boyut                      | 40,00        |
| Körük Sayısı               | 0,0          |
| Bağlantı                   | G1/4"-F      |



### Tasarım verileri

|                    |          |
|--------------------|----------|
| Yükseklik H        | 36,10 mm |
| Nominal çap dn     | 6,75 mm  |
| Diş G1             | G1/4"-F  |
| Diş uzunluğu LG1   | 15,0 mm  |
| Anahtar boyutu SW1 | 22,0 mm  |
| Yay stroku Z       | 7,1 mm   |
| Çap Ds             | 41,3 mm  |
| Çap Dmax(S)        | 45,4 mm  |

Tasarım verileri SAX 40 ED-85 G1/4-IG RP



[WWW.SCHMALZ.COM/10.01.19.00180](http://WWW.SCHMALZ.COM/10.01.19.00180)

Art.-Nr.: 10.01.19.00180



## Teknik veriler

|                                    |                       |
|------------------------------------|-----------------------|
| Vantuz malzemesi                   | Elastodur ED          |
| Malzeme sertliği [Shore A]         | 85,0 Shore A          |
| İş parçası yarıçapı dak (dışbükey) | 25,0 mm               |
| Emme kuvveti (-600mbar)            | 69,00 N               |
| Ağırlık                            | 38,30 g               |
| Yanal kuvvet                       | 49,0 N                |
| Yanal kuvvet yağlı yüzey           | 71,0 N                |
| Cilt                               | 8,500 cm <sup>3</sup> |
| Boyut                              | 40,00                 |
| Körük Sayısı                       | 0,0                   |
| Bağlantı                           | G1/4"-F               |
| Ürün ailesi                        | SAX                   |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



31.12.2026



[WWW.SCHMALZ.COM/10.01.19.00180](http://WWW.SCHMALZ.COM/10.01.19.00180)