


Art.-Nr.: 10.01.19.00215

**Технические данные**

Attribute	Value
Материал присоски	Эластодур ED
Твердость материала [Shore A]	85.0 Shore A
размер	50.00
Количество складок	0.0
Соединение	G1/4"-M

SAX 50 ED-85 G1/4-AG

Присоска SAX, доступная в различных диаметрах, доставляется с соединительным ниппелем, вулканизированным в эластомерную часть.

**Конструктивные данные**

Attribute	Value
Высота H	29.60 mm
Номинальный диаметр dn	6.10 mm
Резьба G1	G1/4"-M
Длина резьбы LG1	14.5 mm
Размер гаечного ключа SW1	22.0 mm
Ход пружины Z	8.4 mm
Диаметр Ds	51.5 mm
Диаметр Dmax(S)	58.4 mm

Конструктивные данные SAX 50 ED-85 G1/4-AG



Art.-Nr.: 10.01.19.00215



Технические данные

Attribute	Value
Материал присоски	Эластодур ED
Твердость материала [Shore A]	85.0 Shore A
Радиус заготовки мин. (выпуклый)	25.0 mm
Всасывающая сила (-600 мбар)	109.00 N
Вес	34.7 g
Поперечная сила	74.0 N
Поперечная сила маслянистой поверхности	110.0 N
Объем	15.200 cm ³
размер	50.00
Количество складок	0.0
Соединение	G1/4"-M
Семейство продуктов	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00215

