




SAX 60 ED-85 M10-AG

Çeşitli çaplarda mevcut olan SAX vantuz, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	60.00
Körük Sayısı	0.0
Bağlantı	M10-M



Tasarım verileri SAX 60 ED-85 M10-AG

Tasarım verileri

Attribute	Value
Yükseklik H	33.40 mm
Nominal çap dn	4.10 mm
Diş G1	M10-M
Diş uzunluğu LG1	14.5 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	10.9 mm
Çap Ds	61.5 mm
Çap Dmax(S)	69.7 mm

Art.-Nr.: 10.01.19.00223



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
İş parçası yarıçapı dak (dışbükey)	30.0 mm
Emme kuvveti (-600mbar)	154.00 N
Ağırlık	38.5 g
Yanal kuvvet	107.0 N
Yanal kuvvet yağlı yüzey	155.0 N
Cilt	25.200 cm ³
Boyut	60.00
Körük Sayısı	0.0
Bağlantı	M10-M
Ürün ailesi	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00223



WWW.SCHMALZ.COM/10.01.19.00223