




SAX 80 ED-85 M10-AG

Çeşitli çaplarda mevcut olan SAX vantuz, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.



Tasarım verileri SAX 80 ED-85 M10-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	80,00
Körük Sayısı	0,0
Bağlantı	M10-M

Tasarım verileri

Attribute	Value
Yükseklik H	34,50 mm
Nominal çap dn	4,10 mm
Diş G1	M10-M
Diş uzunluğu LG1	14,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	13,9 mm
Çap Ds	81,0 mm
Çap Dmax(S)	92,2 mm

Art.-Nr.: 10.01.19.00372



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
İş parçası yarıçapı dak (dışbükey)	32,5 mm
Emme kuvveti (-600mbar)	270,00 N
Ağırlık	44,00 g
Yanal kuvvet	192,0 N
Yanal kuvvet yağlı yüzey	269,0 N
Cilt	51,000 cm ³
Boyut	80,00
Körük Sayısı	0,0
Bağlantı	M10-M
Ürün ailesi	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00372



WWW.SCHMALZ.COM/10.01.19.00372