




SAX 115 ED-85 M10-AG

Çeşitli çaplarda mevcut olan SAX vantuz, elastomer parçaya vulkanize edilmiş bağlantı nipelini ile birlikte teslim edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	115,00
Körük Sayısı	0,0
Bağlantı	M10-M



Tasarım verileri SAX 115 ED-85 M10-AG

Tasarım verileri

Attribute	Value
Yükseklik H	42,60 mm
Nominal çap dn	4,10 mm
Diş G1	M10-M
Diş uzunluğu LG1	14,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	20,2 mm
Çap Ds	116,0 mm
Çap Dmax(S)	129,4 mm

Art.-Nr.: 10.01.19.00367



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
İş parçası yarıçapı dak (dışbükey)	50,0 mm
Emme kuvveti (-600mbar)	549,00 N
Ağırlık	73,50 g
Yanal kuvvet	390,0 N
Yanal kuvvet yağlı yüzey	584,0 N
Cilt	142,000 cm ³
Boyut	115,00
Körük Sayısı	0,0
Bağlantı	M10-M
Ürün ailesi	SAX

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.19.00367



WWW.SCHMALZ.COM/10.01.19.00367