

Art.-Nr.: 10.01.27.01764



VOC-AD-S-100-A

The Vacuum Operation Center is supplied as a ready-to-connect product.


Available spare parts: Proximity switch, vacuum gauge, filter insert, sieve insert, oil, pinch valve, accessories, vacuum pump

Technical data

Attribute	Value
Rated power at 50 Hz	2.70 kW
Voltage at 50 Hz	330 - 400 V - three phase A.C.
Suction rate (max.)	100.000 m ³ /h
Reservoir volume	60.0 l
Function	automatic drain
Length L	940.00 mm
Width B	1,000.00 mm
Height H	2,200.00 mm

Design data

Attribute	Value
Length L1	1,000.00 mm
Length L	940.00 mm
Width B	1,000.00 mm
Height H	2,200.00 mm
Outside diameter D1	32.0 mm
Outside diameter D	32.00 mm



Design data VOC-AD-S-100-A



Art.-Nr.: 10.01.27.01764

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.27.01764**Ordering Data Spare Parts 10.01.27.01764**

Typ		Artikelnummer
Proximity switch	NAEH-SCHA 24V-DC	21.01.09.00060
Vacuum gauge	VAM 67 V H-SE BAR/PSI	10.07.02.00016
Accessories	ZUB BEL EVE-OG 63/100-AC3	22.09.03.00024
Vacuum pump	EVE-OG 100 AC3 AQUA IE3	10.03.02.00094
Filter insert (round)	FILT-EINS 77x90 PE WAS-ABS	10.07.01.00310
Sieve insert	SIEB-EINS 36x 50 VOC	10.01.27.01621
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055
Pinch valve	QV G1-IG	10.05.06.00086
Pinch valve	QV G3/8-IG	10.05.06.00085

