

Needle gripper SNG-M 4 0.8



Art.-Nr.: 10.01.29.00001



Technical data

Attribute	Value
Number of needles	4
Needle diameter	0.8 mm
Pressure range (operating pressure) [bar]	4.0 ... 6.0 bar
Needle stroke Z(NA)	3.0 mm


SNG-M 4 0.8

Needle gripper SNG-M is delivered assembled. The assembly consists of:

- Gripper of type SNG-M

Available spare parts: needle module

Available accessories: mounting plate (BEF-PL)



Design data

Attribute	Value
Length L	35.00 mm
Width B	32.50 mm
Height H	25.00 mm
Thread G1	M5-F
Hole spacing Y1	20.0 mm
Hole spacing X1	20.0 mm
Insertion angle W(E)	30.0 °
Needle stroke Z(NA)	3.0 mm
Thread G4	M4-F

Design data SNG-M 4 0.8



WWW.SCHMALZ.COM/10.01.29.00001

Needle gripper

SNG-M 4 0.8



Art.-Nr.: 10.01.29.00001



Technical data

Attribute	Value
Weight	80.0 g
Installation position	BEL
Number of needles	4
Needle diameter	0.8 mm
Pressure range (operating pressure) [bar]	4.0 ... 6.0 bar
Operating temperature	5 ... 60 °C
Product family	SNG-M



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.29.00001



Ordering Data Accessories 10.01.29.00001

Typ		Item number
Mounting plate	BEF-PL 31x34x11.5 G1/4-IG SNG	10.01.29.00093
Plug union, elbow	STV-W M5-AG 6	10.08.02.00296
Plug union, straight	STV-GE M5-AG 6	10.08.02.00201
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002



Ordering Data Spare Parts 10.01.29.00001

Typ		Item number
Set of spare parts needle gripper	ERS SNG-M 4 0.8	10.01.29.00094



WWW.SCHMALZ.COM/10.01.29.00001